




## UNIT FOR LOCKING PLASTIC HANGERS IN ORDER TO FACILITATE THE POSITIONING OF ARTICLES

This device allows to use most of the hangers existing on the market and accepts all shapes and thicknesses !. : **FAST & VERY FLEXIBLE !!!**

### Very Simple To Use :

*The adjustment of the clamp spacing and the inclination of the working area are rapidly achieved in seconds by the operator and without using a set of tools, which allows different types of workstation dispositions.*

- As it is **entirely pneumatic**, this device needs low maintenance and is very reliable.
- **Very easy to install** (only 4 screws needed to fix the device on a working table).



### Operating method :

1/ The operator positions the hanger in the clamps and if needed adjusts the clamp spacing in order to adapt to the shape or size of the hanger. Then the hanger is locked as soon as the operator pushes on the foot pedal (picture A).

2/ The operator positions the article on the hanger, which is locked in position (picture B). When the article is positioned on the hanger, the operator pushes again on the foot pedal and the hanger and article are freed (picture C).



**APPLICATION** : underwear, panties, corsetry, shorts etc.